

Technical Data

Color	Green
Sizes Available	OS
Packaging	Boxed
Packed	8/Case
Case Weight (lbs)	0.00
Country of Origin	Mexico
Anchor Type	Temporary
Connector Type	Steel
Certifications	TAA Compliant



Miller®

Temporary Webbing Anchor with Rebar Hook and D-Ring

- ANSI Z359-2007 compliant temporary anchor
- Durable webbing construction for demanding worksites
- Rebar hook for easy attachment to larger structures
- Integrated D-ring for secure tie-off connection
- Portable and lightweight for quick setup

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
480-Z7/19INGN	Green	OS	612230153847		