
Carmen | E24964-WTBKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Poetic and organic in design, the undulating form of the metal shade appears to float effortlessly on a slender frame. Abstract discs of LED lighting are encased in round, adjustable heads so that the light can be directed upwards for indirect lighting reflected on the internal white painted face of the shade or the light sources can be rotated downward to provide bright illumination exactly where needed. The simple, sculptural form adds dimension in its scale evocative of a manta ray or the seductive quality of a woman wearing a large floppy hat.



MEASUREMENTS

DIMENSION	: 16.5" L x 16.5" W x 6" H
MAX OAH	: 51.75" OAH
CANOPY	: 6.25" W x 1.75" H x 6.25" L
HANGING WEIGHT	: 6.1 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 560 Rated (420 Del.)
BULB	: 1 x 7W LED PCB Integrated , 7W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Black / Gold (BKGLD)

MATERIAL

Steel, Aluminum

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 30
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com