

SOLARA

555-33-VPB

Solara captures the quiet poetry of a solar system in motion; celestial, geometric, and gently luminous. Inspired by constellations, each cloud seedy glass shade glows like a radiant star, suspended in orbit by slender rods finished in Vintage Patina Brass. The 3- and 5-light chandeliers feature diamond-shaped shades that create dimensionality from every perspective, while the single-light pendant drops like a sculptural earring. The result is lighting that feels both architectural and romantic. They are designed not just to illuminate, but to bring a sense of wonder to the everyday.

FINISHES

VINTAGE POLISHED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 65.5"

Width/Diameter: 32.75"

Canopy/Backplate: 7"

Product Weight: 19lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Seeded Cloud

Shade 1 Top Width: 12"

Shade 1 Height: 14.75"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 46

Bulb Quantity: 5

Wire Length: 144"

Cord Type: LOW VOLTAGE DC WIRE

Dimmer Type: TRIAC, 0-10 VOLT

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 2750

Title 24: No

Field Serviceable: Yes



SHIPPING

Carton 1: 43" x 30" x 16"

Carton 1 Weight: 26lb

Shipping Method: Ground

Country of Origin: VN