Dorian | E21352-PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A bold and timeless collection, Dorian features a square block support with two cylinder LED tubes that extend horizontally. The tubes rotate individually to position light making it perfect for highlighting artwork and collectibles in stairwells or walls. The collection features elongated linear and vertical pendants, picture lights and damp rated sconces. The wall-mounted sconces have streamlined back plates that are either square or round that can mount to a single gang junction box or common 3-0 or 4-0 boxes with cover plate included. Two options for extension including one that extends less than four inches for ADA compliance. Available in Matte Black, Polished Chrome, and plated Gold, this collection is a subtle, handsome design with timeless appeal.



MEASUREMENTS

DIMENSION	: 22.5" W x 3" H x 3.5" Ext
MAX OAH	: 4.75" W x 4.75" H
HANGING WEIGHT	: 2.64 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,050 Rated (750 Del.)
BULB	: 1 x 15W LED PCB Integrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: ELV or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION

Black (BK)
Gold (GLD)
Polished Chrome (PC)

MATERIAL

Aluminum, Acrylic, Steel

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: ANY
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com