SCHAEFER®


Versa-Kool® VKM24-O 24" Mobile OSHA-Compliant Circulation Fan—5640 CFM, 1/2 HP, 115 Volt



- HEAVY-DUTY—great for warehouses or large outdoor spaces
- LEGENDARY—greater air movement and superior cooling
- BEST-IN-CLASS—high-density polyethylene housing
- Heavy-duty 1/2 HP motor and galvanized steel blades
- Includes a 2-year limited warranty

Product Description

Reduce heat stress and improve air quality with Schaefer's uniquely designed circulation fan. Unrivaled in the market, these fans are engineered to produce greater air movement and superior cooling no matter the application. You don't hear them. You don't see them. You only feel them! Also known as Horizontal Air Flow (HAF) fans, these fans move air in a coherent horizontal pattern creating a gentle 'racetrack' air flow pattern needed in greenhouses to maximize heat distribution and humidity control by mixing the air, from ceiling to floor.



©2024 Pinnacle Climate Technologies

Features and Benefits

- Deep guard design for unmatched performance, low noise levels and safety without sacrificing airflow
- Matched high quality motors and blades for maximum efficiency
- Powder coated steel guards for increased durability and corrosion resistance
- Powder coated steel mounting bracket and power cord included
- Wide variety of mounting options available for flexible and easy installation
- Misting kits available for even greater cooling
- Assembled in the USA
- 2-year limited warranty

Key Specs

Model Number	VKM24-O
Brand	Schaefer® Versa-Kool®
Warranty	2-year limited warranty
Net Weight (lb.)	55
Air Flow (CFM)	5640
Motor Size (HP)	1/2
Fan Diameter (in.)	24
Variable Speed	No
Speed (RPM)	1075
Thrust (lbf)	3.18
Volts	115
Amps	5.2

Schaefer is a registered trademark of Pinnacle Climate Technologies, Inc.

©2024 Pinnacle Climate Technologies