



Post Office Box 97
Benton Harbor, Michigan
Ph: 616/926-6171
Fax: 616/925-8288

PART NUMBER:

LTD187

REV.

A

Product Specifications

MODEL NUMBER	RPM		HP	kW	NET WT.	
	60 cycle	50 cycle			lbs.	kg
2565-V2A	1725	1425	1.5	1.1	38	15.9
* 2565-V89A	1725	1425	1.5	1.1	38	15.9

SOUND LEVEL 77 dB(A) MAX.
NORMAL AMBIENT 1°C - 40°C
RELATIVE HUMIDITY 8% - 100% NON CONDENSING
ENVIRONMENT CLEAN DUST FREE

NOTES:

1. TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.
2. DIMENSIONS: METRIC (mm) U.S. IMPERIAL (inches).
3. * DENOTES INACTIVE MODEL.

