

SONNY

F2860-BRL

Sonny takes inspiration from a mid-century sputnik chandelier, reimagined with an organic, staggered rhythm. Finished in Bronze Leaf, slender arms extend outward, culminating in a softly glowing cloud seedy glass globe. The seemingly randomized arrangement creates a dynamic, almost celestial composition. Available as a 4-light sconce and a 12- or 20-light chandelier, Sonny serves as a stunning centerpiece for dining or living spaces.

FINISHES

BRONZE LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 21.5"

Width/Diameter: 59.75"

Minimum Height: 28"

Maximum Height: 69.75"

Canopy/Backplate: 6"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 45.1lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Seeded Cloud

Shade 1 Top Width: 5.5"

Shade 1 Height: 5"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 20

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 65" x 65" x 28"

Carton 1 Weight: 73lb

Shipping Method: Truck Only

Country of Origin: PH