

MAEVE

HL1112201-AGB/CYM

The Maeve table lamp elevates an understated silhouette with an artistic floral design. Reminiscent of hand-painted vases, the soft pastel Maybell Motif glaze traces the base with floral forms. Topped with a wide white linen shade, Maeve diffuses light in a calm, even glow.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS w/ Ceramic Maybell Motif
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20.25"
Width/Diameter: 16"
Canopy/Backplate: 5.5"
Product Weight: 7lb
Canopy/Backplate Shape: Oval
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Textile
Shade 1 Finish: White Linen
Shade 1 Top Width: 15"
Shade 1 Bottom L/W: 0" / 16"
Shade 1 Height: 9"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Wire Length: 96"
Cord Type: SPT-2 SILVER
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 18" x 18" x 25"
Carton 1 Weight: 16lb
Shipping Method: Ground
Country of Origin: VN

