



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**65-1170** - 105/90/70 Watt LED Linear High Bay;  
3K/4K/5K CCT; IP69K; 120-347 Volt; White Finish



**GENERAL**

|                           |                                      |
|---------------------------|--------------------------------------|
| Company                   | NUVO                                 |
| EA Height                 | 3.94                                 |
| EA Width                  | 14.57                                |
| EA Length                 | 17.52                                |
| Bulb Included             | Integrated                           |
| Chain Length (in)         | 41                                   |
| Dimmable Text             | 0-10V Dimming                        |
| Material                  | Aluminum                             |
| Fixture Type              | Linear Hi-Bay                        |
| Status                    | Active                               |
| Surge Protection          | Built-in surge protection - 6KV      |
| Total Harmonic Distortion | <20%                                 |
| CCT Selectable            | Yes                                  |
| Wattage Selectable        | Yes                                  |
| Finish Family             | White                                |
| Additional Info           | Default Wattage: 105W                |
| Amps                      | 0.880-0.300/0.750-0.260/0.580-0.200A |
| Integrated Features       | Integrated Sensor Port               |
| Lens Finish               | Opaque                               |
| Lens Material             | Polycarbonate (PC)                   |
| Lensed                    | Yes                                  |
| Power Factor              | >0.9                                 |
| SDS Class                 | LED_Fixture                          |
| Product Technology        | LED                                  |
| Fluor Equiv               | 135W-190W                            |

**ELECTRICAL**

|                     |                             |
|---------------------|-----------------------------|
| CCT (Kelvin Temp)   | 3000K/4000K/5000K           |
| Dimmable            | Yes-Dimmable                |
| Hours Rated         | 50000                       |
| Beam Angle (degree) | 90                          |
| Color Temp          | Soft White to Natural Light |
| CRI                 | 80+                         |
| Dimming Type        | 0-10V Dimming               |
| Operating Frequency | 50/60Hz                     |
| Operating Temp      | -40C (-40F) to +55C (+131F) |
| HID Equivalent      | 200W                        |
| Lumens              | 15900L-11200L               |
| Volts               | 120V-347V                   |
| Watts               | 105W/90W/70W                |

**PHYSICAL**

|               |       |
|---------------|-------|
| Finish        | WHITE |
| Housing Color | White |

**ADDITIONAL INFO**

|          |         |
|----------|---------|
| Warranty | 5-Years |
|----------|---------|

**PACKAGING**

|               |                |
|---------------|----------------|
| UPC           | 045923413254   |
| Case Cube     | 0.582          |
| Case Height   | 3.94           |
| Case Length   | 17.52          |
| Case Quantity | 1              |
| Case UPC      | 10045923413251 |
| Case Weight   | 12.8           |
| Case Width    | 14.57          |
| EA Cube       | 0.582          |
| EA Height     | 3.94           |
| EA Length     | 17.52          |
| EA Quantity   | 1              |
| EA Weight     | 12.8           |
| EA Width      | 14.57          |
| Pack Type     | Box            |
| Web Height    | 2.44           |
| Web Length    | 16.77          |
| Web Width     | 13.78          |

**COMPLIANCE**

|                 |                   |
|-----------------|-------------------|
| Bug Rating      | B4-U2-G2          |
| CA Prop 65      | Lead              |
| DLC ID          | S-5KLYJB          |
| FCC Compliant   | Yes               |
| IP Rating       | IP69K             |
| Location Rating | Wet               |
| NSF Approved    | Yes               |
| ROHS Compliant  | Yes               |
| Safety Listing  | cULus - Certified |
| California Ban  | Lawful for sale   |
| DLC Approved    | Yes               |
| Title 20        | Exempt            |
| T24 Compliant   | No                |