

# AUGER BITS



## Auger Bits

- Patented, self-feeding screw point tip draws the bit completely through the wood – no need to push the bit while drilling
- Design/Cutting Edge feature
- Over-center flude design for fast chip evacuation – no clogging or chip flyback
- Made from hardened carbon alloy steel for durability and longer life
- 7/16" hex shank with quick-change groove for impact drivers
- Nail Eater® design with patented cutting edge cuts nails and staples
- Nail Eater® bits made in the USA
- See "Bit Extensions" if more length is required (see page 115)



## Nail Eater® Extreme

- 7-5/8" (5" twist) and 18" (15" twist) lengths available

### NAIL EATER® EXTREME

CAT. NO.	UPC NO.	BULK CAT. NO.	BULK UPC NO.	BULK QTY.	HOLE DIA.		HEX SHANK	
					IN	mm	IN	mm
66PT-1/2	783310309154	–	–	–	1/2	12.7	5/16	7.9
66PT-5/8	783310309192	–	–	–	5/8	15.9	7/16	11.1
66PT-11/16	783310309215	–	–	–	11/16	17.5	7/16	11.1
66PT-3/4	783310309239	66PT-B-3/4	783310366591	24	3/4	19.1	7/16	11.1
66PT-13/16	783310020066	–	–	–	13/16	20.6	7/16	11.1
66PT-7/8	783310309277	66PT-B-7/8	783310366621	24	7/8	22.2	7/16	11.1
66PT-15/16	783310309291	–	–	–	15/16	23.8	7/16	11.1
66PT-1	783310309314	66PT-B-1	783310366645	24	1	25.4	7/16	11.1
66PT-1-1/8	783310309352	–	–	–	1/8	28.6	7/16	11.1
66PT-1-1/4	783310309376	–	–	–	1-1/4	31.8	7/16	11.1

### SHORT NAIL EATER® EXTREME

CAT. NO.	UPC NO.	BULK CAT. NO.	BULK UPC NO.	BULK QTY.	HOLE DIA.		HEX SHANK	
					IN	mm	IN	mm
62PTS-5/8	783310317883	–	–	–	5/8	15.9	7/16	11.1
62PTS-11/16	783310317906	–	–	–	11/16	17.5	7/16	11.1
62PTS-3/4	783310317920	62PTS-B-3/4	783310366409	12	3/4	19.1	7/16	11.1
62PTS-13/16	783310317944	–	–	–	13/16	20.6	7/16	11.1
62PTS-7/8	783310317968	62PTS-B-7/8	783310366423	12	7/8	22.2	7/16	11.1
62PTS-1	783310317982	62PTS-B-1	783310366430	12	1	25.4	7/16	11.1
61/62PTS-1-1/8	783310304319	–	–	–	1-1/8	28.6	7/16	11.1
61/62PTS-1-1/4	783310304333	–	–	–	1-1/4	31.8	7/16	11.1