






PRODUCT DESCRIPTION

Softly rounding forms are constructed of outdoor-rated concrete molds. Finished in Greystone or Chalky White, these sconces are both playful and sophisticated. A diagonal reveal along the fixture's body emits light while also casting light above and below the fixture.



MEASUREMENTS

DIMENSION	: 6" L x 6" W x 12" H x 4" Ext
BACK PLATE	: 5.12" W x 0.63" H x 6" HCO
HANGING WEIGHT	: 5.6 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,260 Rated (600 Del.)
BULB	: 1 x 18W LED DC Integrated , 18W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up/Down

FINISHES OPTION

Chaulk White (CHK)

MATERIAL

Concrete, SS, Glass

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com