
Cuff | E22945-BKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

Varied lengths of Matte Black cylinders feature a cuffed edge in Gold and suspend on thin black wire. Available in multiple configurations, this integrated LED pendant collection provides an attractive design for economical pricing.



MEASUREMENTS

DIMENSION	: 15.75" L x 15.75" W x 8.75" H
MAX OAH	: 129.5" OAH
CANOPY	: 15.75" W x 1.5" H x 15.75" L
HANGING WEIGHT	: 9.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,600 Rated (1,200 Del.)
BULB	: 5 x 8W LED DC Integrated , 40W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black / Gold (BKGLD)

MATERIAL

Steel, Polycarbonate

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com