



3 Year Limited Warranty

**SILICON
CARBIDE**

41-414 Specifications *Grainger Part#5JA31*

Factory part number	Operating voltage	Lead wire temperature rating	Wire gauge	Lead wire length	Connector type	Included hardware
217NM	120V AC (including 208/240V rated models)	392°F / 200°C	18 AWG	5¼ in. (133 mm)	Receptacle with .093 in. male pins	Special mounting adaptors



Replacement Information

DiversiTech®	IGN-1F 700-3, IGN-1R 700-4, IGN-2 700-5, IGN-001
Supco®	SSN2000, IG4000, IG414

41-418 Specifications

Factory part number	Operating voltage	Lead wire temperature rating	Wire gauge	Lead wire length	Connector type	Included hardware
271NM	120V AC (including 208/240V rated models)	392°F / 200°C	18 AWG	5¼ in. (133 mm)	Molex side lock connector	Bracket



Replacement Information

Supco®	IG418
--------	-------

41-419 Specifications

Factory part number	Operating voltage	Lead wire temperature rating	Wire gauge	Lead wire length	Connector type	Included hardware
	120V AC (including 208/240V rated models)	392°F / 200°C	18 AWG	5 in. (127 mm)	Receptacle with .093 in. male pins	None



Replacement Information

White-Rodgers™	767A-357
----------------	----------