

An accelerator and latex free nitrile glove to prevent skin allergies.

TEGERA® 842

Learn more

FOR PROTECTION OF SENSITIVE HANDS

A disposable and very flexible nitrile glove with excellent fingertip sensitivity. Accelerator-free and latex-free to prevent skin allergies. Made of 0.07 mm/2,75 mils nitrile with structured palm for improved grip. Chlorinated and non-powder. 100 pieces/box. 10 boxes/carton.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Perfect fit
- Extra comfortable
- Light

FUNCTIONS

- Approved for handling foodstuffs
- Inside chlorinated
- For touchscreen
- Latex-free
- Waterproof
- Elastic
- Accelerator-free
- Thin

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Risk of infection, Contact with moisture, Contact with damp, Contact with oil

PRIMARY ENVIRONMENTS OF USE

Microbiological risk environments, Disposable use, Moist environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Care work, Cleaning, Fine assembly, Food handling, Hotel- and restaurant work, Kitchen work, Service work

PRIMARY INDUSTRIES OF USE

Accommodation and food service (HoReCa), Food and beverage processing, Public safety, security and defence

TYPE OF WORK

Light weight

CHEMICAL RESISTANCE

According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION

TYPE Disposable gloves - General protection
CATEGORY Cat. III
THICKNESS 0,07
LENGTH 240 mm
DEXTERITY 5
INSIDE Non powder
GRIP DESIGN Structured
COLOUR Purple
QUANTITY PER PACK 100 Pieces
PACKS PER: BUNDLE/CARTON Not sold in bundle/10
DISPLAY TYPE Box
DIPPING MATERIAL Nitrile
CUFF STYLE Rolled edges

COMPLIANCE

CE 2777

EAC TP TC 019:2011

EN ISO 21420:2020

EN ISO 374-5:2016 Virus

EN ISO 374-1:2016+A1:2018 Type B KPT

FEATURES

General Protection

For touchscreen

Waterproof

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	K	P	T
Permeation level	6	2	4
Degradation %	-16,0	26,8	34,0

SIZE		ARTICLE NUMBER	EAN
7	S	842-7	7340118381589
8	M	842-8	7340118381701
9	L	842-9	7340118381824
10	XL	842-10	7340118381947

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.