Rinkle | E24878-133FG

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An airy arrangement of abstract forms, the Rinkle pendants feature sheets of transparent acrylic shaped by hand. The light guided acrylic captures the glow of energy efficient LEDs recessed within strips of shining stainless steel, obscuring the source of illumination. Delicately suspended by a series of thin wires, the pendants appear to be floating in an adjustable configuration of weightless light sculpture. Available in Polished Chrome, French Gold, and Brushed Gunmetal, its unique design adds a showstopping element to interior spaces.



*max overall height

MEASUREMENTS

DIMENSION	: 35.5" L x 23.5" W x 15.75" H
MAX OAH	: 135.5" OAH
CANOPY	: 23.5" W x 1.5" H x 35.5" L
HANGING WEIGHT	: 42 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,880 Rated (1,620 Del.)
BULB	: 2 x 2.4W LED PCB Integrated , 36W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV (Phase Dim)
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Brushed Gunmetal (BGM)
French Gold (FG)
Polished Chrome (PC)

GLASS

Patterned Acrylic 133

MATERIAL

Stainless Steel, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

ADJUSTABLE
RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com