Project / Job Name:

Location:

Fixture Type:

Notes:



67-561 - Running Man Green Exit Sign; 120/347V; 2HR backup; Single/Dual Face; Universal Mounting; Wet Location; Low Temperature; White Finish

WET LOCATION · RoHS COMPLIANT · IP 65

GENERAL

Company	SATCO
EA Height	13.39
EA Width	3.43
EA Length	9.06
Bulb Included	Integrated
Material	Thermo Plastic
Fixture Type	Exit Sign
Product Notes	Ni-Cad Battery; 120 minute discharge time; 24 Hour Recharge Time
Status	Active
Style	Utility
Total Harmonic Distortion	35%-45%
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Additional Info	Low Temperature Model
Amps	0.023/0.008A
Has Camera	No
IOT Enabled	No
Power Factor	0.75
SDS Class	LED_Fixture
Sloped Ceiling Compatible	No
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

Dimmable	Non-Dimmable
Operating Frequency	60Hz
Operating Temp	-13F to +122F (-25C to +50C)
Volts	120V/347V
Watts	2.8W
Battery Chemistry	Ni-Cad

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Universal

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923675911
Case Cube	1.7235
Case Height	9.84
Case Length	21.65
Case Quantity	6
Case UPC	10045923675918
Case Weight	31.97
Case Width	13.98
EA Cube	0.2408
EA Height	13.39
EA Length	9.06
EA Quantity	1
EA Weight	4.7
EA Width	3.43
Pack Type	Box
Web Height	8.86
Web Width	13.0

COMPLIANCE

CA Prop 65	Lead
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	CSAus
California Ban	Non-Compliant
Title 20	No
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026