



jalas® M-SPORT 3460A LIGHT SPORT

ASTM F2413-18 M/I/C/SD 35 EN ISO 20345:2011 S2, SRC

Learn more

Safety shoe, toecap material aluminium, plastic shank, PU outsole, upper material split leather, Textile

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Good shock absorption

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Polstered shaft edge
- Ventilating insole
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)
- Water repellent

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
FITTING Regular
COLLECTION M-Sport
UPPER MATERIAL Split leather, Textile
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS FX2 Classic
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Shock absorption zone in Ergothan
OUTSOLE MATERIAL PU outsole
FASTENING Laces
SHOELACES LENGTH 100 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.04 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35

EAC

EN ISO 20345:2011
S2, SRC

TP TC 019:2011

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	3460A-36	6408487413841
37	4	5	6	3460A-37	6408487413858
38	5	5.5	6.5	3460A-38	6408487413865
39	6	6.5	7.5	3460A-39	6408487413872
40	6.5	7.5	8.5	3460A-40	6408487413889
41	7	8	9	3460A-41	6408487413896
42	8	9	10	3460A-42	6408487413902
43	9	9.5	11	3460A-43	6408487413919
44	10	10.5	11.5	3460A-44	6408487413926
45	10.5	11	12.5	3460A-45	6408487413933
46	11	12	13	3460A-46	6408487413940
47	12	13	14	3460A-47	6408487413957

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.