



P65

Technical Data



Color	Dark Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.46 x 13.94 x 16.34
Case Weight (lbs)	15.43
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Semi-Rimless
Lens Color	Light Gray
Frame Fit	Universal
Lens Coating	FogLess 3Sixty, Anti-Scratch
Bridge	Rubber
Temple	Molded
Base Curve	8.5
Certifications	ANSI Z87.1, TAA Compliant

Bouton® Optical Xtricate™

Semi-Rimless Safety Glasses with Dark Blue Frame, Light Gray Lens and FogLess® 3Sixty™ Coating

- Rubber nose pads offer a more secure fit
- Lightweight, semi-rimless design provides all day user comfort
- Flexible temples provide a secure fit without uncomfortable pressure points
- FogLess® 3Sixty™ enhanced hydrophobic action resists lens fogging and provides clear vision in extreme working conditions
- 8.5 Base curve lens
- Meets ANSI Z87.1-2015 standards
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Outdoor Work
- Construction Applications
- Public Works

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-59-0520	Dark Blue	Clear	Clear	FL360/AS	616314267246	01616314267245	02616314267244
250-59-0521	Dark Blue	Tinted	Green	FL360/AS	616314267253	01616314267252	02616314267251
250-59-0551	Dark Blue	Tinted	Light Gray	FL360/AS	616314267260	01616314267269	02616314267268

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated