Sonata | E24775-133BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Composed of gently curving aluminum channels in Matte Black that supports a patterned translucent acrylic arranged in groups of vertical stripes, this series of pendants and coordinating ADA sconce expresses a musical quality in brilliant LED light. The wall sconce visibly suggests the shape of a piano, while the pendants return inward where they bend at the ends in an instrumental, elegant shape. A story told in simple forms, the collection is illuminated by dedicated LED light sources concealed within the frames enhancing the translucent undulating slabs of patterned acrylic. Their sculptural form is sure to add wonder to both classical and modern settings.



MEASUREMENTS

DIMENSION	: 59" L x 17" W x 6" H
MAX OAH	: 126" OAH
CANOPY	: 6" W x 2.25" H x 6" L
HANGING WEIGHT	: 11.25 lb

LAMPING

INPUT VOLTAGE	: 120-277VV
LUMENS	: 2,940 Rated (1,420 Del.)
BULB	: 1 x 42W LED DC Integrated , 42W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

GLASS

Patterned Acrylic 133

MATERIAL

Aluminum,Steel,Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com