

A comfortable and certified occupational shoe that makes you feel good when you take care of others.

jalas® SPOC 5492

ASTM F2892-18 SD 35 EN ISO 20347:2012 01, SRC, FO, A, E

Learn more

FOR THE HEALTHCARE SECTOR, WITH LACES

A lightweight certified shoe with high breathability for use in healthcare work environments. The shoe is tested and approved for slip-resistance and has shock-absorbing soles in multiple layers for personal protection. Textile mesh fabric with high breathability makes the shoe cool, and the laces and elastic tongue attachment gives a smooth fit. The sock-like construction increases comfort. ESD certified for protection of sensitive electronic equipment. All models are unisex.

CHARACTERISTICS

- Excellent grip
- Perfect fit
- Extra comfortable
- Breathable
- Excellent shock absorption
- Light

FUNCTIONS

- Breathable mesh
- Low weight
- Anti-static properties
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Sprain injuries, Antistatic, Slipping, Strain injuries

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Office environments, Slippery environments

PRIMARY AREAS OF USE

Care work, Healthcare

SPECIFICATION

TYPE Occupational footwear, Low shoes
CATEGORY Cat. II
FITTING Regular
COLLECTION SpOc
UPPER MATERIAL Textile
LINING MATERIAL Polyester
INSOLE JALAS FX2 Pro SpOc
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL EVA
OUTSOLE MATERIAL Nitrile rubber outsole
SHOELACES LENGTH 110 cm
COLOUR White
NET WEIGHT, (SIZE 42) 0.74 kg

COMPLIANCE

CE Cat. II

ASTM F2892-18
SD 35

EAC

EN ISO 20347:2012
01, SRC, FO, A, E

TP TC 017:2011

FEATURES

Anti-static properties

Ergothan Shock Absorption System

ESD

Oil-resistant outsole

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	5492-35	6408487533082
36	3	4	5	5492-36	6408487533129
37	4	5	6	5492-37	6408487533167
38	5	5.5	6.5	5492-38	6408487533204
39	6	6.5	7.5	5492-39	6408487533242
40	6.5	7.5	8.5	5492-40	6408487533280
41	7	8	9	5492-41	6408487533327
42	8	9	10	5492-42	6408487533365
43	9	9.5	11	5492-43	6408487533402
44	10	10.5	11.5	5492-44	6408487533440
45	10.5	11	12.5	5492-45	6408487533488
46	11	12	13	5492-46	6408487533525
47	12	13	14	5492-47	6408487533563
48	13	13.5	14.5	5492-48	6408487533600

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.