

EVANDER

477-42-VGL/GSW

Combining straight lines and curved forms, Evander is all about balance. The stacked, gesso white bowls are filled with light, reflecting upon each other to create a tranquil glow. Organic shaping in the connection points softens the overall impression of the slender framework. Evander is available as a 6 or 10-light chandelier and a 2-light wall sconce.

FINISHES

VINTAGE GOLD LEAF w/ GESSO WHITE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 29.5"

Width/Diameter: 42"

Minimum Height: 37.25"

Maximum Height: 79"

Canopy/Backplate: 5.75"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 33lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 84

Bulb Quantity: 6

Bulb Included: Yes

Wire Length: 120"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"):

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 4725

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 48" x 48" x 34"

Carton 1 Weight: 61lb

Shipping Method: Truck Only

Country of Origin: PH

