



Technical Data

Color	Gray
Sizes Available	OS
Packaging	Bagged Pair
Packed	200/Case
Case Dimensions (in)	23.20 x 14.60 x 21.00
Case Weight (lbs)	17.99
Country of Origin	China
Lens	Indoor Outdoor
Frame Style	Rimless
Lens Color	Gray
Lens Coating	Anti-Scratch,
Bridge	Molded
Certifications	ANSI Z87.1, CSA Z94.3 Certified

UVEX® A700

Rimless Gray Frame with I/O Lens and Anti-Scratch Hardcoat

- Affordably priced for all of your work environments
- Aggressive styling provides a stylish fit for your everyday wearer
- Slim sizing fits small or narrow facial profiles
- Lightweight design, flexible temples and soft temple tip pads provide a secure, wraparound fit and all-day comfort
- Molded universal nose bridge provides a comfortable fit
- All lenses provide 99.9% UV protection
- Meets ANSI Z87.1+
- Meets CSA Z94.3

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
A704	Gray	I/O	Gray	AS/	040025108558	30040025108559	70040025108557
A704-EH	Gray				198987170332	10198987170339	20198987170336

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated