SIEMENS

Data sheet US2:PN1224B1100C

SIEMENS LOW VOLTAGE PLUG-ON NEUTRAL READY PRO SERIES ASSEMBLED LOAD CENTER. MAIN BREAKER WITH 12 1-INCH SPACES ALLOWING MAX 24 CIRCUITS. 1-PHASE 3-WIRE SYSTEM RATED 120/240V (100A) 22KAIC. SPECIAL FEATURES: COPPER BUS, GREY TRIM NEMA TYPE 1 ENCLOSURE FOR INDOOR USE.

General technical data	
configuration of the busbars	COPPER BUS
number of circuits in a trunking unit	24
phase number	1
suitability for operation	RESIDENTIAL AND LIGHT COMMERCIAL ELECTRIC DISTRIBUTION
Electricity	
ampacity	100 A
voltage between phase and Ground (GND) rated value	120 V
voltage between phase and phase rated value	240 V
Model	
product brand name	SIEMENS
product sub brand name	LOAD CENTERS
product type designation	PLUG-ON NEUTRAL READY PRO SERIES
special product feature	GREY TRIM
Mechanical Design	
number of modular width units for installation width	12
size of the circuit-breaker	100A
General product approval	
certificate of suitability	UL

last modified: 7/9/2021

Subject to change without notice
© Copyright Siemens