

3M™ Value Masking Tape 101+

The basic tape for basic jobs.

You never know when you'll need to tape something. That's why 3M™ Value Masking Tape 101+ is the perfect addition to toolboxes, job sites and workplaces.

Intended for light-duty indoor use, this tape is ideal for marking, temporary holding, wrapping, sealing and masking. It sticks instantly to paper, metal, wood, plastic, glass and many other clean surfaces and resists lifting or curling for consistent reliability.



Versatile

Instant stick and easy hand tearability make this a useful tape for applications such as bundling cords and wires, temporary labeling, overwrapping, light masking and attaching notes.



Cost-effective

Keep it handy as a simple solution for many everyday applications such as light-duty attachment and temporary holding, sealing and covering on the assembly line or at the job site.



Easy to apply

Easy, controlled unwind prevents shredding and splintering while the hand-tearable crepe backing conforms to a variety of surfaces and around corners.



Versatile and reliable.

When you're looking for a cost-effective tape for light duty applications, look no further than 3M™ Value Masking Tape 101+. For more information on 3M Masking Solutions, contact your local 3M representative or call 1-800-362-3550 or visit 3M.com/masking.



Product	UPC#	Width	Length	Rolls/Case
3M™ Value Masking Tape 101+ Bulk	00-689330-20540-0	12 mm	55 m	72
	00-689330-20543-1	18 mm	55 m	48
	00-689330-20544-8	24 mm	55 m	36
	00-689330-20545-5	36 mm	55 m	24
	00-689330-20546-2	48 mm	55 m	24
	00-689330-20547-9	72 mm	55 m	12
	00-689330-20548-6	96 mm	55 m	8

Specifications

Total Thickness: 5.1 mil (0.13 mm)
Adhesion to Steel: 34 oz/in (3.7 N/cm)
Tensile Strength: 22 lb/in (38.6 N/cm)
Elongation at Break: 9%



Closure and Masking Systems Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 877-369-2923 (Fax)
3M.com/masking

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for proper evaluation (including, but not limited to, fitness for purpose and suitability of application), selection, and use of 3M products. Safety products should always be selected and used in accordance with all applicable regulations and standards (e.g., OSHA, ANSI, and others), after conducting a proper hazard assessment. Failure to properly evaluate, select, and use a 3M product may result in injury, sickness, death, and/or harm to property. Dispose of used atomizing heads, residual paint/coatings, used containers/materials, and PPS in accordance with local regulations.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

3M is a trademark of 3M Company. Please recycle. Printed in USA.
© 3M 2021. All rights reserved. 70-0716-1650-5 REV 8/21