



022-5293

Northstar Coastal Edge 30' SS Cable SRL

FEATURES :

- Exclusive cable retraction limiter
- Simplified cable replacement system
- Semi-sealed mainspring
- Semi-sealed pawl assembly
- Oscillating, double-locking/anti-ratcheting pawls
- 360/180° swivel attachment point w/alu carabiner
- Lifeline handle w/ mini absorber and indicating stainless steel swivel snap hook
- RFID equipped for easy asset tracking
- All components are Z359.12 compliant

Eligible for service and repair

Class

2

Anchor above or below dorsal D-ring



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.14-2021
OSHA	1910.140, 1910.66

ANSI CLASS 1	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	≤ 42 in. (107 cm)
Actual arrest distance	≤ 41 in. (104 cm)
Max. free fall distance	24 in. (61 cm)
Min. required fall clearance	6 ft. 11 in. (2.1 m)
For full clearance requirements, see user instructions	

ANSI CLASS 2	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	N/A
Actual arrest distance	89 in. (226 cm)
Max. free fall distance	72 in. (183 cm)
Min. required fall clearance	15 ft. 11 in. (4.9 m)
For full clearance requirements, see user instructions	

MATERIAL SPECIFICATION	
Cable	13/64" stainless steel
Carabiner	Aluminum
Housing	Polycarbonate
Load-Indicating Swivel Snap Hook	Stainless steel
Shock pack	Polyester

