

Product Specifications



#10 x 1-1/2" Slotted Hex Washer Head Metal Piercing Screw

Part Number SP10112

UPC 781002849919

Sharpeez Screws are manufactured with sharp points used to pierce thin sheet metal and are capable of making their own mating threads. They are manufactured with a 5/16" hex head designed to resist stripping and are commonly used for sheet metal applications, HVAC work, plumbing, and electrical.



Physical Characteristics

Type	Sharpeez Screw
Drive Type	Slotted
Head Type	Hex Washer
Thread Type	DWF
Point Type	Sharp
Size	#10 x 1-1/2"
Dia./Thread Size	#10
Hex Size	5/16"
Length (in)	1-1/2"
Thread Pitch\Thread Per Inch	15
Drive Size	#2
Material	Carbon Steel
Finish	Zinc Plated

Performance Data

Special Features	Ultra-sharp piercing point, Double-lead speed thread, Non-walking piercing point, Ideal for sheet metal, Zinc-plated finish
Applications	Sheet Metal, HVAC, Plumbing, and Electrical

Packaging Details

Standard Qty	100
Sleeve Qty	500
Master Qty	3000
Price Per	100
Package Length	2.25
Package Width	3.00
Package Height	4.25
Package Weight	.70

Certifications

UNSPSC	31161506
RoHS Compliant	Yes