

GARETH

B6723-PBR/TBK

Drawing inspiration from traditional lanterns, this family of sleek exterior fixtures includes sconce and a portable lantern in multiple sizes. Elongated silhouettes and a mixed-finish combination of Textured Black and Patina Brass give these lanterns a contemporary update. While Gareth is equipped with a single chunky pillar candle for a timeless look, the light source is actually a lightweight aluminum puck with LED technology housed the bottom of the glass cylinders. Gareth is available as both a sconce and a portable lantern in multiple sizes. The portable option is rechargeable and includes a convenient handle for easy transport.

FINISHES

PATINA BRASS w/ TEXTURE BLACK

Coastal Suitable Finish (EPM): No



GARETH

B6723-PBR/TBK

DIMENSIONS

Height: 23"
Width/Diameter: 6.25"
Canopy/Backplate: 6.25"
Product Weight: 9.28lb
Extension: 7.25"
Top to Center: 3.75"
Canopy/Backplate Shape: Rectangle
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: Yes

Shade

Shade 1: Glass
Shade 1 Finish: Clear
Shade 1 Top Width: 5.75"
Shade 1 Height: 17.25"
Shade 2: Glass
Shade 2 Finish: Clear
Shade 2 Top Width: 6"
Shade 2 Height: 17.25"

ELECTRICAL



Bulb 1

Bulb Included: N/A
Socket: Integrated LED
Bulb Type: LED
Max Wattage: 8
Bulb Quantity: 1
Bulb Included: Yes
Wire Length: 7"
Cord Type: B & W TEFLON W/ GROUND WIRE
Dimmer Type: ELV, TRIAC
Gem Box Required (2"x3"): No
Dark Sky: No
CRI: 90
Color Temp.: 3000k
Lumens: 300
Title 24: No
Field Serviceable: No

SHIPPING

Carton 1: 13" x 14" x 32"
Carton 1 Weight: 13lb
Shipping Method: Ground
Country of Origin: CN