



## TEGERA® 910

Learn more

## NO DIPPING, GOOD FINGERTIP FEEL

A soft and flexible liner glove with CRF® technology and cut protection level C. Without dipping for good fingertip feel. Color with high visibility. Suitable for all-round work such as assembly, inspection, sheet metal work, and workshop tasks in dry environments.

### CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Comfortable
- Breathable

### FUNCTIONS

- High visibility colour
- Soft

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations

## PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments

## PRIMARY AREAS OF USE

Assembly, Inspection work, Sheet-metal work, Engineering, Metalwork, Glass industry work, Repair work

## PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Public safety, security and defence, Transport equipment manufacturing

## TYPE OF WORK

Medium weight

## SPECIFICATION

**TYPE** Cut resistant gloves
**CATEGORY** Cat. II
**KNITTING GAUGE (GG)** 13
**LINING MATERIAL** CRF® Technology, Glass fibre thread, HPPE, Polyester, Spandex
**LENGTH** 220-270 mm
**DEXTERITY** 5
**COLOUR** Orange
**PAIRS PER: BUNDLE/CARTON** 12/120
**DISPLAY TYPE** Bulk pack
**CUFF STYLE** Knitwrist cuff
**CUFF MATERIAL** Textile
**CUT RESISTANCE (EN ISO 13997)** Cut resistance level C
**CUT RESISTANCE (EN ISO 13997) TDM:** 12.9 N
**OUTER MATERIAL SPECIFICATION** HPPE (High performance polyethylene), Polyester, Glass fibre thread, Natural latex, Elastane

## COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 2X4XC

ANSI A2 CUT

ANSI 3 ABR

## FEATURES

Cut protection

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 5 | XXS | 910-5 | 7340118332734 |
| 6 | XS | 910-6 | 7392626074552 |
| 7 | S | 910-7 | 7392626074576 |
| 8 | M | 910-8 | 7392626074668 |
| 9 | L | 910-9 | 7392626074613 |
| 10 | XL | 910-10 | 7392626074514 |
| 11 | XXL | 910-11 | 7392626074538 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*