SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



65-750 - LED Small Round Wall Pack; 20W; CCT Selectable; Bypassable Photocell; 120-277 Volt; Black Finish

WET LOCATION · DIMMABLE · FC · RoHS COMPLIANT · CCT SELECTABLE · 50,000 HOURS · AIR TIGHT · IP 65 · 0-10V DIMMING

GENERAL

Company	NUVO
EA Height	3.62
EA Width	8.94
EA Length	8.94
Bulb Included	Integrated
Diameter	8.7
Extends (in)	3.4
Material	Die-cast Aluminum
Fixture Type	Area Light
Status	Active
Style	Modern and Contemporary
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	15%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	Black
Additional Info	UV stabilized powder coated finish
Amps	0.167-0.072A
Has Camera	No
Integrated Features	Integrated Photocell
IOT Enabled	No
Photo Cell	Yes - Bypassable
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	150W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	100
Color Temp	Warm to Cool White
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-22F to +113F (-30C to +45C)
HID Equivalent	100W
Lumens	2600L-2800L
Volts	120V-277V
Watts	20W
Max Lumens	2800L
Connection	Direct Wired

PHYSICAL

Lamp Base	Integrated
Finish	BLACK
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round
Mounting Procedure	Wall

ADDITIONAL INFO

Warranty	5-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923657689
Case Cube	1.9751
Case Height	9.72
Case Length	18.98
Case Quantity	10
Case UPC	10045923657686
Case Weight	28.49
Case Width	18.5
EA Cube	0.1674
EA Height	3.62
EA Length	8.94
EA Quantity	1
EA Weight	2.64
EA Width	8.94
Pack Type	Color Box
Web Height	8.7
Web Width	8.7

COMPLIANCE

ADA Compliant	Yes
Air Tight	Yes
Bug Rating	B1-U3-G2
CA Prop 65	Lead
DLC ID	PLGEPXY78U37
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026