





PRODUCT DESCRIPTION

Pullman offers effortless adjustability in architectural accent lighting. A sleek retractable arm glides from a 90 degree wall position to a full downward aim with no visible hardware. The precision mechanism allows seamless repositioning for both task and ambient light while preserving a clean silhouette. A slightly recessed LED GU10 lamp in a beveled trim reduces glare and simplifies maintenance. Finished in Natural Aged Brass, Satin Nickel, or Matte Black, Pullman is both functional and beautifully refined.

MEASUREMENTS

DIMENSION	: 2.25" L x 2.25" W x 6.75" H
MAX OAH	: 48.75" OAH
CANOPY	: 5" W x 0.75" H x 5" L
HANGING WEIGHT	: 6.6 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 600 Rated (500 Del.)
BULB	: 1 x 7W LED BL7GU10CL120V30 , 7W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Natural Aged Brass (NAB)

Satin Nickel (SN)

MATERIAL

Aluminum, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com