Stormy | E20497-MPLT

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Evocative of turbulent skies, Stormy is a sculptural masterwork that transforms negative space into visual drama. A billowing cluster of stainless-steel spheres, finished in a moody interplay of Black Nickel, French Gold, and Polished Chrome, creates an abstract cloudscape of extraordinary depth. Floating among the forms, matte white glass globes in varying sizes emit a layered, ambient glow, while discreet canopy-mounted downlights provide refined functionality. Offered in two commanding sizes, Stormy is both art and atmosphere--an expression of elemental motion rendered with impeccable precision.



*max overall height

MEASUREMENTS

DIMENSION	: 35.5" L x 28.75" W x 22.5" H
MAX OAH	: 142.75" OAH
CANOPY	: 10.25" W x 2" H x 10.25" L
HANGING WEIGHT	: 52.8 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 3,600 Rated (1,800 Del.)
BULB	: 12 x 44W LED DC Integrated , 45W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Multi-Plated (MPLT)

MATERIAL

Stainless Steel, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com