



CT663BKADA



32.38" x 23.63" x 23.5" (H x W x D)

24" wide residential ENERGY STAR certified 5 cu.ft. refrigerator-freezer made in Europe in a black finish and ADA compliant height

Highlights:

ENERGY STAR certified for guaranteed savings and a greener performance

32" height for use in ADA compliant settings

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

Product Features:

24" Wide European ADA Height Refrigerator-Includes a full refrigerator and freezer section for undercounter use
Freezer

Peak24 Series	European-made collection for recessed installation featuring large capacity interiors, ENERGY STAR certified performances, and versatile style
ENERGY STAR certified	Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs
ADA Compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Slim counter height dimensions	Ideal 24" footprint offers full 5.1 cu.ft. storage capacity in a slim fit
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Dual evaporator cooling	Our unique and efficient design separately cools the refrigerator while maintaining a lower temperature in the freezer compartment by utilizing two evaporators
Adjustable glass shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup
Door shelves	Store tall bottles and condiments right on the door for convenient access



CT663BKADA Specifications:

Overview	
Nominal Height	32.0" (81 cm)
Height of Cabinet	32.0" (81 cm)
Height to Hinge Cap	32.38" (82 cm)
Nominal Width	24.0" (61 cm)
Width	23.63" (60 cm)
Nominal Depth	24.0" (61 cm)
Depth	23.5" (60 cm)
Depth with door at 90°	45.38" (115 cm)
Capacity	5.04 cu.ft. (143 L)
Defrost Type	Cycle
Door	Black
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	330.0kWh/year
Amps	1.2
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs. (45 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101068497
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Wine Bottle Shelving	Yes
Interior Light	Yes
Refrigerator - Interior Height	18.0" (46 cm)
Refrigerator - Interior Width	21.0" (53 cm)
Refrigerator - Interior Depth	18.0" (46 cm)
Refrigerator - Capacity	4.5 cu.ft
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2

Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.25" (13 cm)
Freezer - Interior Width	19.0" (48 cm)
Freezer - Interior Depth	11.5" (29 cm)
Freezer - Capacity	0.6 cu.ft
Thermostat Type	Dial
Refrigerant Type	R600a
Refrigerant Amount	0.92 oz.
High Side PSI	180.0
Low Side PSI	80.0
Compressor Step Height	5.5" (14 cm)
Compressor Step Width	21.0" (53 cm)
Compressor Step Depth	6.0" (15 cm)

