






PRODUCT DESCRIPTION

A sculptural take on classic form, Rubelle pairs gentle curvature with purposeful design. Its bulbous oval shade is suspended by an arched backplate and adjustable arm, allowing the light to be positioned closer to its subject. The name merges "Rubin" and "Belle"--a nod to graceful proportions and timeless beauty. Whether mounted as a portrait light, vanity fixture, or bookshelf accent, Rubelle offers quiet drama and tailored sophistication.



MEASUREMENTS

DIMENSION	: 25.5" L x 1.75" W x 1" H x 9.25" Ext
MAX OAH	: 5" W x 2.75" H
HANGING WEIGHT	: 3.3 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 800 Rated (500 Del.)
BULB	: 1 x 19W LED PCB Integrated , 19W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: TriacÂ orÂ ELVÂ atÂ 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000-3500-4000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)

Gold (GLD)

MATERIAL

Aluminum, Acrylic

RATINGS

cETLus

Damp Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 30000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com