Alumilux Sideline - Bath Vanity |
E42661-SBR

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Pure geometry, tailored for the bath. The Sideline Vanity light extends a streamlined aluminum bar that washes light in both directions, creating a clean, modern effect. A simple color temperature selectable switch toggles through five color temperatures - 2700 K, 3000 K, 3500 K, 4000 K, and 5000 K - so you can match the mood or task at hand. Finished in luxurious Natural Aged Brass or crisp Polished Chrome, this design is also available as an outdoor-rated sconce finished in powder-coat options that offers that same seamless look throughout the home, see Sideline: Outdoor.



MEASUREMENTS

DIMENSION	: 18" L 4.75" H x 3" Ext
BACK PLATE	: 4.75" W x 5.75" H x 9" HCO
HANGING WEIGHT	: 1.76 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,260 Rated (820 Del.)
BULB	: 2 x 9W LED AC Integrated , 18W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Polished Chrome (PC)
Satin Brass (SBR)

MATERIAL

Aluminum, PC

RATINGS

cETLus
Damp Location
CA Title 24
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical/Horizo
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com