

BIRMINGHAM

512-05-VPB

FINISHES

VINTAGE POLISHED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 40.25"

Width/Diameter: 20.75"

Canopy/Backplate: 7"

Product Weight: 22.7115lb

Extension: 5.75"

Top to Center: 20.25"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Topaz

Shade 1 Top Width: 7.5"

Shade 1 Height: 1.75"

Shade 2: Glass

Shade 2 Finish: Clear Etched

Shade 2 Top Width: 5.5"

Shade 2 Height: 1"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Bulb Type: LED

Max Wattage: 40

Bulb Quantity: 5

Bulb Included: Yes

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: TRIAC, 0-10 VOLT

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 1250

Title 24: No

Field Serviceable: Yes

SHIPPING

Carton 1: 38" x 24" x 14"

Carton 1 Weight: 34lb

Shipping Method: Ground

Country of Origin: VN

