

# VERNAZZA

536-24-VPB

Combining minimalist and maximalist elements, the Vernazza flush mount evokes tension through duality. Designed as a close-to-ceiling fixture, it delivers the visual punch of a chandelier. The oversized ceiling pan forms a radiant frame for a ring of ribbed glass globes, nodding to Art Deco aesthetics. Available with 8 or 12 lights and finished in Vintage Patina Brass, this joyful statement piece will enliven an entryway or living room.

## FINISHES

### VINTAGE POLISHED BRASS

Coastal Suitable Finish (EPM): No

## DIMENSIONS

Height: 7.25"

Width/Diameter: 23.5"

Canopy/Backplate: 20"

Product Weight: 17lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

## Shade

Shade 1: Glass

Shade 1 Finish: Clear Etched Optic Rib

Shade 1 Top Width: 6.25"

Shade 1 Height: 6"



## ELECTRICAL



### Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 8

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

## SHIPPING

Carton 1: 26" x 26" x 12"

Carton 1 Weight: 25lb

Shipping Method: Ground

Country of Origin: VN