Project / Job Name:

Location:

Fixture Type:

Notes:

62-8012 - Cosmos; Medium LED Pendant; Matte Black Finish; Frosted Acrylic Lens



GENERAL

Company	NUVO
EA Height	7.87
EA Width	34.65
EA Length	34.65
Mounting Height	1.63
Mounting Length	8.25
Mounting Width	8.25
Bulb Included	Integrated
Diameter	31.25
Material	Aluminum / Steel
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<10%
Up Down Installation	Down
Wire Color	Black
CCT Selectable	Yes
Wattage Selectable	No
Collection	Cosmos
Finish Family	Black
Amps	1.600A
Lens Finish	Frosted
Lens Material	Acrylic
Lensed	Yes
Power Factor	>0.9
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	180W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K
Dimmable	Yes-Dimmable
Hours Rated	25000
Beam Angle (degree)	120
Color Temp	Warm White to Neutral White
CRI	90+
Dimming Type	Phase cut
Operating Frequency	50/60Hz
Operating Temp	-4F to +140F (-20C to +60C)
Lumens	5360L
Volts	120V-277V
Watts	67W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Matte Black
Housing Color	Matte Black
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	3-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416385
Case Cube	5.4681
Case Height	7.87
Case Length	34.65
Case Quantity	1
Case UPC	10045923416382
Case Weight	20.24
Case Width	34.65
EA Cube	5.4681
EA Height	7.87
EA Length	34.65
EA Quantity	1
EA Weight	20.24
EA Width	34.65
Pack Type	Kraft Box
Web Height	14.0
Web Width	31.25

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026