

NAXOS

552-30-VGL

An ode to craftsmanship, the Naxos family is adorned with loosely draped strands of hand-carved coco shell pieces. The layering of smaller shell elements on each strand adds depth and volume, giving this family a sense of movement and a handcrafted beauty. Shaped like petals, the tonal pieces bring life to each design, including a 2-light wall sconce, a chandelier in three sizes, and an island light.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 29.5"

Width/Diameter: 30"

Minimum Height: 53.25"

Maximum Height: 99"

Canopy/Backplate: 7"

Hanging Type: 18-8" Stems

Product Weight: 36lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Wood

Shade 1 Finish: Coco Shell

Shade 1 Top Width: 3"

Shade 1 Height: 12"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 12

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 34" x 34" x 34"

Carton 1 Weight: 58lb

Shipping Method: Truck Only

Country of Origin: PH

