



P65

Technical Data



Bouton® Optical Mag Readers™

Semi-Rimless Safety Readers with Black Frame, Clear Lens and Anti-Scratch Coating - +1.00 Diopter

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	24.92 x 10.00 x 12.40
Case Weight (lbs)	12.79
Country of Origin	Taiwan
Lens	Clear
Frame Style	Semi-Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Rubber Tips
Diopter	Yes
Base Curve	8
Certifications	ANSI Z87.1, TAA Compliant

- Magnification reader glasses are for the worker who needs to see up close
- The 30 mm wide "curved top" reading magnifier provides the worker with enough lens area to view his work throughout the day
- Durable nylon frame with extra wide latex-free rubber nose pads for more comfort when working up close
- Temples with soft rubber pads provide a secure fit
- 8 Base curve lens
- +1.00 Diopter
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-25-0010	Black	Clear	Clear	AS	616314064630	01616314064639	02616314064638
250-25-0015	Black	Clear	Clear	AS	616314036118	01616314036118	02616314036118
250-25-0020	Black	Clear	Clear	AS	616314036125	01616314036125	02616314036125
250-25-0025	Black	Clear	Clear	AS	616314036132	01616314036132	02616314036132
250-25-0030	Black	Clear	Clear	AS	616314036149	01616314036149	02616314036149
250-25-0115	Black	Tinted	Gray	AS	616314036156	01616314036156	02616314036156
250-25-0120	Black	Tinted	Gray	AS	616314036163	01616314036163	02616314036163
250-25-0125	Black	Tinted	Gray	AS	616314036170	01616314036170	02616314036170
250-25-0130	Black	Tinted	Gray	AS	616314036187	01616314036187	02616314036187
250-25-1515	Black	Clear	Clear	AS/AF	616314186257	01616314186256	02616314186255
250-25-2020	Black	Clear	Clear	AS/AF	616314186264	01616314186263	02616314186262
250-25-2525	Black	Clear	Clear	AS/AF	616314186271	01616314186270	02616314186279

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated