



Assurance®

12 Mil Butyl Rubber Glove with Smooth Grip-14"

- 12 Mil Bromine-Butyl Rubber ideal for incidental splash and acute chemical exposure
- The addition of bromine enhances temperature resistance, offering superior durability
- Designed to handle extreme exposure to exposure to polar organic compounds such as ketones, carboxylic acids, esters, and amine derivatives
- 14 " length for extended forearm protection
- Smooth Grip
- Tested to EN 16350 for electrostatic properties to help protect any static sensitive materials or equipment



Technical Data

Color	Black
Sizes Available	7-11
Polymer	Butyl
Thickness	12 Mil
Lining	Unlined
Length	14"
Cuff	Rolled
Grip	Smooth
Construction	Unsupported, ESD Safe
Case Dimensions (in)	22.83 x 14.96 x 7.48
Case Weight (lbs)	0.00
Packed	48 Pair/Case
Packaging	Bagged Pair
Certifications	TAA Compliant, EN 16350
Country of Origin	Germany

Performance Data

EN 374	ABIKNOT
EN 388	001X
EN 374-5	Bacteria, Fungi and Virus

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
BUT03/7	Black	7	616314941320	10616314941327	20616314941324
BUT03/8	Black	8	616314941405	10616314941402	20616314941409
BUT03/9	Black	9	616314941481	10616314941488	20616314941485
BUT03/10	Black	10	616314941528	10616314941525	20616314941522
BUT03/11	Black	11	616314941566	10616314941563	20616314941560