



Bouton® Optical Lady Eva®

Rimless Safety Readers with Clear / Pink Temple, Clear Lens and Anti-Scratch Coating - +2.50 Diopter

- Designed for the worker who needs to see up close
- Offered in increments of +0.25 diopters to give users the exact reading power of their personal glasses
- Eva's construction better fits the facial structure of a woman
- Lightweight, rimless design provides all day user comfort
- Pink rubber co-molded temples provide a secure fit
- Molded nose bridge design to fit the vast majority of users
- 10 Base curve lens
- +2.50 Diopter
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

Technical Data

Color	Pink
Sizes Available	OS
Packaging	Bagged Each
Packed	72 Pair/Case
Case Dimensions (in)	25.59 x 10.24 x 12.60
Case Weight (lbs)	13.23
Country of Origin	Malaysia
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Narrow Face
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Rubber Tips
Diopter	2.50
Base Curve	10
Construction	Womans Fit
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-11

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-12-0100	Pink	Clear	Clear	AS	616314062490	01616314062499	02616314062498
250-12-0125	Pink	Clear	Clear	AS	616314062506	01616314062505	02616314062504
250-12-0150	Pink	Clear	Clear	AS	616314062513	01616314062512	02616314062511
250-12-0175	Pink	Clear	Clear	AS	616314062520	01616314062529	02616314062528
250-12-0200	Pink	Clear	Clear	AS	616314062537	01616314062536	02616314062535
250-12-0225	Pink	Clear	Clear	AS	616314062544	01616314062543	02616314062542
250-12-0250	Pink	Clear	Clear	AS	616314062551	01616314062550	02616314062559
250-12-0275	Pink	Clear	Clear	AS	616314062568	01616314062567	02616314062566
250-12-0300	Pink	Clear	Clear	AS	616314062575	01616314062574	02616314062573

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated