



YAZV282NTCFX, Cu Compression, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel, 4/0 Flex G, H, I, K, M, DLO, 4/0 AWG

By Burndy

Catalog # [YAZV282NTCFX](#)

4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size Range	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Conductor - Copper Str Compact Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Str Navy Size	200
Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4/0 AWG



Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	"4/0 AWG"
Conductor - Copper Flex I Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Length	5.21 in
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	0.77 in
Package Width	0.000 in
Bolt Size	1/2 in
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Stud Size fraction	1/2

General

Color Code	Purple
Trade Name	HYLUG™
Sub Brand	HYLUG
Die Index	15
UPC	781810165966
Type	Long Barrel, Skive
Material	Copper
Finish Type	Tin-Plated

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	50

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand