



JSP® Evolution® Deluxe 6161

Full Brim Mining Hard Hat with HDPE Shell, 6-Point Polyester Suspension and Wheel Ratchet Adjustment

- Mining lamp bracket is non-corrosive and will receive 99% of the "World's Mining Lamps"
- Cable loop located on the rear of the hard hat keeps the cable in place
- High-Density Polyethylene (HDPE) shell with a full brim providing additional protection against sun, glare, rain and falling debris
- Extended back brim helps protect neck and ears from the sun's UV rays, as well as a run-off for rain and snow...short front brim shades the face while allowing excellent visibility
- Brim includes finger grips on front and rear, as well as a textured underside to reduce reflection/glare
- 6-Point suspension system with polyester textile straps offers unrivaled comfort without compromising performance
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



P65

Technical Data

Color	Neon Yellow, Yellow, Neon Orange, Green, Red, Blue, White
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	21.65 x 12.60 x 17.91
Case Weight (lbs)	10.36
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Sweatband	Chamlon
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6161M-50	Blue	OS	616314164613	01616314164612	02616314164611
280-EV6161M-30	Green	OS	616314164606	01616314164605	02616314164604
280-EV6161M-OR	Neon Orange	OS	616314164637	01616314164636	02616314164635
280-EV6161M-LY	Neon Yellow	OS	616314168000	01616314168009	02616314168008
280-EV6161M-60	Red	OS	616314164620	01616314164629	02616314164628
280-EV6161M-10	White	OS	616314153570	01616314153579	02616314153578
280-EV6161M-20	Yellow	OS	616314168017	01616314168016	02616314168015