

White coloured glove for fine precision work where great dexterity is desirable.

TEGERA® 778

Learn more

OUR THINNEST, WITH SMOOTH PU DIPPING

Our thinnest glove suitable for fine precision work. Great dexterity and tactility thanks to ultra-thin 18 gg knitting technology. Thin PU coating on palm for better grip and abrasion protection. White colour for clean tasks.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Good grip
- Extra comfortable

FUNCTIONS

- Ultra thin
- Super soft

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Drying out

PRIMARY ENVIRONMENTS OF USE

Dry environments, Clean environments, Moist environments

PRIMARY AREAS OF USE

Fine assembly, Painting

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 18
LINING MATERIAL Nylon
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR White
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Nylon
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018
2110X

ANSI 2 ABR

SIZE		ARTICLE NUMBER	EAN
5	XXS	778-5	7340118325422
6	XS	778-6	7340118324098
7	S	778-7	7340118324104
8	M	778-8	7340118324111
9	L	778-9	7340118324128
10	XL	778-10	7340118324074
11	XXL	778-11	7340118324081

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.