PRODUCT INFORMATION PACKET

Model No: 612A
Catalog No: 612A
1/15 HP Refrigeration Motor, 1550 RPM, 115/208-230 Volts, 42 Frame, OAO

Refrigeration Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	**1/15 Hp**	Output KW	**0.05 kW**
Frequency	**60 Hz**	Voltage	**115/208-230 V**
Current	**2.8/1.4 A**	Speed	**1550 rpm**
Service Factor	**1**	Phase	**1**
Duty	**Air Over**	Insulation Class	**A**
Frame	**42Y**	Enclosure	**Open Air Over**
Thermal Protection	**Automatic**	Ambient Temperature	**40 °C**
UL	**Recognized**	CSA	**Y**
CE	**N**	Number of Speeds	**1**

Technical Specifications

Electrical Type	**Shaded Pole**	Starting Method	**Across The Line**
Poles	**4**	Rotation	**Clockwise Lead End**
Mounting	**Resilient Rings**	Motor Orientation	**Horizontal**
Drive End Bearing	**Sleeve**	Opp Drive End Bearing	**Sleeve**
Frame Material	**Rolled Steel**	Shaft Type	**Flat**
Overall Length	**8.87 in**	Frame Length	**3.92 in**
Shaft Diameter	**0.375 in**	Shaft Extension	**3.3 in**
Outline Drawing	**DA2E7129-S01**		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/07/2022