SIEMENS

Data sheet US2:P1E18MC250CT



Siemens Low Voltage RP1 Unassembled Lighting Panel. Dimensions (H x W x D) IN: 32.0 x 20.0 x 5.75. 3-Phase 4-Wire allows 18 circuits user selects Main Device (Lug/Breaker). Rated 480Y/277V (250A). Special features: tin-plated copper main bus, subfeed space included

suitability for operation	Lighting Loads/ Branch Circuit Loads
product brand name	SIEMENS
product type designation	UPB interiors
material of the enclosure	Copper BUS
certificate of suitability	PB1/UL67

last modified: 4/8/2020

Subject to change without notice
© Copyright Siemens