

BELLUNO

533-28-VGL

Airy and textural, Belluno's tiered composition pairs sculptural volume with a lightness of material. Made from pleated white paper, each layer brings a soft sense of translucency and movement. The Vintage Gold Leaf finish on the chain, ceiling canopy, and lower cap adds an elegant contrast to the crisp white folds. Available as a 2-light and 3-light chandelier, Belluno sets a soft ambience as light shines through its paper construction.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20.25"

Width/Diameter: 28"

Minimum Height: 24"

Maximum Height: 94.25"

Canopy/Backplate: 6.5"

Hanging Type: 72" Chain

Product Weight: 7lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: Handmade Paper

Shade 1 Top Width: 17.5"

Shade 1 Bottom L/W: 0" / 4.25"

Shade 1 Height: 6.5"

Shade 2: Textile

Shade 2 Finish: Handmade Paper

Shade 2 Top Width: 22.75"

Shade 2 Bottom L/W: 0" / 6.25"

Shade 2 Height: 6.75"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 2

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 32" x 32" x 28"

Carton 1 Weight: 33lb

Shipping Method: Truck Only

Country of Origin: PH

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993