



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**65-1160** - LED UFO Hi-Bay; 200/150/100 Wattage Selectable; 4000K/5000K CCT Selectable; 120-277 Volt; White Finish



**GENERAL**

Company	NUVO
EA Height	5.83
EA Width	15.94
EA Length	15.94
Bulb Included	Integrated
Diameter	14.99
Dimmable Text	0-10V Dimming
Material	Die-cast Aluminum
Fixture Type	UFO Hi-Bay
Product Notes	6 Foot Whip
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	<20%
Wire Color	White
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Additional Info	Metal Halide Equivalence: 200W-450W
Amps	0.917/1.375/1.833A
Integrated Features	Integrated Sensor Port
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Lensed	Yes
Power Factor	>0.9
SDS Class	LED Fixture
Indoor Outdoor	Indoor
Product Technology	LED

**ELECTRICAL**

CCT (Kelvin Temp)	4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	85
Color Temp	Cool White/Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40C (-40F) to +50C (+122F)
HID Equivalent	225W-375W
Lumens	30000L/22500L/15000L
Volts	120V-277V
Watts	200W/150W/100W

**PHYSICAL**

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

**ADDITIONAL INFO**

Warranty	5-Years
----------	---------

**PACKAGING**

UPC	045923410147
Case Cube	0.8572
Case Height	5.83
Case Length	15.94
Case Quantity	1
Case UPC	10045923410144
Case Weight	13.12
Case Width	15.94
EA Cube	0.8572
EA Height	5.83
EA Length	15.94
EA Quantity	1
EA Weight	13.12
EA Width	15.94
Pack Type	Box
Web Height	6.07
Web Width	14.99

**COMPLIANCE**

CA Prop 65	Lead
DLC ID	S-NFKXMB
FCC Compliant	Yes
IP Rating	IP69K
Location Rating	Wet
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24 Compliant	No