Smokestack | E26144-142BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Segmented glass cylinders in a grey Smoke Gradient filter nostalgic tubular LED lamps. The Matte Black frame adds a dark contrast providing ambient light as a guide to your exterior. Select from 3 sizes of wall sconces, all wet rated.



MEASUREMENTS

DIMENSION	: 6" W x 16.75" H x 6" Ext
BACK PLATE	: 6" W x 0.75" H x 8.25" HCO
HANGING WEIGHT	: 7.08 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 590 Rated (400 Del.)
BULB	: 1 x 6W LED E26 Medium , 6W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 2200K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)

GLASS

Graduating Smoke 142

MATERIAL

Steel, Glass

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com