PRODUCT INFORMATION PACKET

Model No: MD5472
Catalog No: MD5472
KRYO™ FORTRESS 415 CFM Refrigeration Fan Pack, 1550 RPM, 90-240 Volts, TEAO, IP66/67



Regal and Genteq are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Motor Type	**Electronically Commutated**	Thermal Protection	**Automatic**
Speed	**1550 rpm**	Number of Speeds	**1**
Phase	**1**	UL	**Yes**
CSA	**Y**		

Technical Specifications

Blower Outlet Shape	**Round**	Motor Enclosure	**Totally Enclosed**
Blower Outlet Flange	**Yes**	Bearing Type	**Ball**
Fan Size	**209.55**	Air Flow	**415**
Voltage Range	**90-240 V**	Current Range	**0.55-0.20 A**
Frequency	**50-60 Hz**	Impeller Type	**Axial**
Number of Fan Blades	**5**	Rotation Direction	**Clockwise Opposite Shaft End**
Ambient Operating Temp Range	**-40C to +55C °C**	Electrical Type	**Electronically Commutated Motor**
ODE Bearing Type	**Ball Bearing**	Insulation Class	**B**
IP Code	**IP66/IP67**	DE Bearing Type	**Ball Bearing**
CE	**N**		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/29/2025